


Swivel arm



Technical data

	Order details	Max. Load capacity	Reach	Recording	Order number
1	Swivel arm with monitor mount	15 kg	508 mm	VESA 75/100	N0872
2	Swivel arm with monitor mount	5 kg	429 mm	VESA 75/100	N0877
3	Support carriage with monitor attachment	15 kg	105 mm	VESA 75/100	N0873
4	Support carriage with monitor attachment	5 kg	64 mm	VESA 75/100	N0878
5	Tablet holder for swivel arm	0.75 kg	–	7 to 10 inch	N0879
6	Swivel arm with keyboard holder 172 x 640 mm	15 kg	528 mm	–	N0874
7	Swivel arm with notebook holder 288 x 400 mm	10 kg	425 mm	–	N0880
8	Swivel arm with rail L350	30 kg	406 mm	–	N3513
9	Swivel arm with rail L500	25 kg	556 mm	–	N3998
10	Swivel arm with shelf L500	25 kg	570 mm	–	N3514
11	Shelf 400 x 300	30 kg	–	–	N3516
12	Swivel arm for KLINK® short	5 kg	429 mm	L 80 mm	S03-001-70
13	Swivel arm for KLINK® long	5 kg	429 mm	L 300 mm	S03-001-71
14	Groove moulding short *	–	–	L 185 mm	S03-001-80
14	Long slot moulding *	–	–	L 425 mm	S03-001-81

* Additional 4x10 mm groove for storage boxes or grab trays (see example 2)

Exemples d’application



Example 1 – Components:
Swivel arm N3513
2x slot moulding long S03-001-81
Perforated panel 450x500mm N3538



Example 2 – Components:
Swivel arm N3513
3x Slotted moulding long S03-001-81
12x Gripper shell N4022



Example 3 – Components:
Swivel arm N3514
Shelf 300 x 400 N3516
Stacking container N4110