

## Raccordements spéciaux

### 6. Raccordements d'onglet doubles

N° de référence							N° de référence									
B01-8	C02-8	A02-8	20*	20	30	40	45	50	50	45	40	30	20*	A02-8	C02-8	B01-8
									A24-10							
									E24-10							
									C24-10							
									B24-10							
									D24-10							
									DD24-10							
									A24-51							
									C24-51							
									B24-51							
*avec perçage 6.0 mm																



### 7. Rallongements de profilé

N° de référence							Profilé avec Base										
B01-8	C02-8	A02-8	20*	20	30	40	45	50	50	45	40	30	Perçage 20 12.1 mm	Perçage 20 6.0 mm	A02-8	C02-8 / CO3-8	B01-8
									A24-00								
									E24-00								
									C24-00								
									B24-00								
									D24-00								
									DD24-00								
									A24-50								
									C24-50								
									B24-50								
*avec perçage 6.0 mm																	



### 8. Raccordements à filet

N° de référence			Profilé avec Base										
Filetage	M6	M8	A	50	45	40	30	Perçage 20 12.1 mm	Perçage 20 6.0 mm	A02-8	C02-8 / CO3-8	B01-8	
A20-66	A20-60		13										
E20-66	E20-60		13										
C20-66	C20-60		13										
B20-66	B20-60		10										
D20-66	D20-60		10										
DD20-66			7										
Sur demande	A20-65												
Sur demande	C20-65												
Sur demande	B20-65												

