




The flexible and modular KANYA KLINK® system, which can be used anywhere, makes it easier to maintain order, an overview, and thus increase productivity.



## KLINK® consoles

Order information 0/45/90°	Dimensions	Carrying capacity	Order number
Console 0/45/90°	300 mm x 150 mm	10 kg	S03-001-01
Console 0/45/90°	150 mm x 300 mm	8 kg	S03-001-02
Console 0/45/90°	300 mm x 300 mm	8 kg	S03-001-03
Console 0/45/90°	450 mm x 300 mm	8 kg	S03-001-04
Console 0/45/90°	300 mm x 450 mm	5 kg	S03-001-05
Console 0/45/90°	450 mm x 450 mm	5 kg	S03-001-06
Order information 0/40/80°	Dimensions	Carrying capacity	Order number
Console 0/40/80°	300 mm x 150 mm	10 kg	S03-001-11
Console 0/40/80°	150 mm x 300 mm	8 kg	S03-001-12
Console 0/40/80°	300 mm x 300 mm	8 kg	S03-001-13
Console 0/40/80°	450 mm x 300 mm	8 kg	S03-001-14
Console 0/40/80°	300 mm x 450 mm	5 kg	S03-001-15
Console 0/40/80°	450 mm x 450 mm	5 kg	S03-001-16



## KLINK® suspension extrusion

Order information 0/45/90°	Dimensions	Order number
Suspension extrusion 0/45/90°	76 mm incl. covering cap	S03-001-30-001
Suspension extrusion 0/45/90°	148 incl. covering cap	S03-001-30-002
Suspension extrusion 0/45/90°	cut to length	S03-001-30-099
Covering cap		C40-19
Order information 0/40/80°	Dimensions	Order number
Suspension extrusion 0/40/80°	76 mm incl. covering cap	S03-001-40-001
Suspension extrusion 0/40/80°	148 mm incl. covering cap	S03-001-40-002
Suspension extrusion 0/40/80°	cut to length	S03-001-40-099
Covering cap		C40-29-L C40-29-R



## KLINK® suspension rail

Order information	Dimensions	Order number
Suspension rail	length 500 mm*	S03-001-50-010
Suspension rail	length 1000 mm*	S03-001-50-020
Suspension rail	length 1500 mm*	S03-001-50-030
Suspension rail, without holes	cut to length	S03-001-50-099
Covering cap		C40-81

\* Hole distance suitable to perforated plate.



## KLINK® shadowboards

Order information
-------------------

Shadowboard

Customized on demand available.



## KLINK® transport trolley

Order information
-------------------

Transport-Trolley

Customized on demand available.