


Plastic hinges fix



Application

That the optimal pivoting characteristics is given for doors, windows ect, the designer needs a selection of hinges, which are fitting exactly.




Specification

PA-GF black
Pin: steel zinc coated

Order data	Order number							
Base	A	B	C	D	E	F	O	
50	76	50	56	30	38	38	6.3	A60-00-PA *
50/30	63	50	43	30	25	38	6.3	AB6-00-PA *
30	50	50	30	30	25	25	6.3	B60-00-PA *

Plastic hinges lift-off type



Whether cost efficient plastic, attractive diecasting, or high-strength Aluminium hinges, the assortment gives you the possibility to do the right choice.




Specification

PA-GF black
Pin: steel zinc coated

Order data	Order number							
Base	A	B	C	D	E	F	O	
50	96	48	55	28	48	48	6.5	A60-60-PA*
50/40	86	48	50	28	48	38	6.5	AC6-60-PA*
50/30	77	48	45	28	48	29	6.5	AB6-60-PA*
40	76	48	45	28	38	38	6.5	C60-60-PA*
40/30	67	48	40	28	38	29	6.5	CB6-60-PA*
30	58	48	35	28	29	29	6.5	B60-60-PA*

* the order number for the fixing kit add
-S to the art.no.:
Example: A60-60-PA-S

Aluminium hinges lift-off type



Whether cost efficient plastic, attractive diecasting, or high-strength Aluminium hinges, the assortment gives you the possibility to do the right choice.



Specification

Al anodised natural colours
Pin: steel zinc coated

Order data	Order number								
Base	A	B	C	D	E	F	O	left	right
Plastic hinges									
50	96	48	55	28	48	48	6.5	A60-60-PA*	A60-61-PA*
50/40	86	48	50	28	48	38	6.5	AC6-60-PA*	AC6-61-PA*
50/30	77	48	45	28	48	29	6.5	AB6-60-PA*	AB6-61-PA*
40	76	48	45	28	38	38	6.5	C60-60-PA*	C60-61-PA*
40/30	67	48	40	28	38	29	6.5	CB6-60-PA*	CB6-61-PA*
30	58	48	35	28	29	29	6.5	B60-60-PA*	B60-61-PA*
Aluminium hinges									
50	92	50	54	30	46	46	6.5	A60-60*	A60-61*
50/40	82	50	49	30	46	36	6.5	AC6-60*	-
50/40	82	50	49	30	36	46	6.5	-	AC6-61*
40	72	50	44	30	36	36	6.5	C60-60*	C60-61*