


Table top



Different table tops can be selected depending on the area of application.



Please use the checklist for the ordering process (see page 56/57).

Technical data

	Description of the	Strength	Max. Size	Colour	Density
1	MDF board, HPL covered incl. ABS edges,	9/13/17/20/26/30 mm	2800 x 1310 mm	Light grey similar	818 kg/m ³
2	Chipboard, HPL covered incl. ABS edges	9/13/17/20/26/30 mm	2800 x 1310 mm	Light grey similar	691 kg/m ³
3	ESD panel, conductive coating incl. edges	26 mm	2000 x 1800 mm	Light grey similar	700 kg/m ³
4	Multiplex board beech, oiled, bevelled edges	30/40/50 mm	3100 x 1830 mm	Natural beech	850 kg/m ³
5	Beech glued, quality A/B, oiled, bevelled edges	19/20/30 mm	2450 x 1250 mm	Natural beech	900 kg/m ³
6	HPL solid core board, bevelled edges	13/16/19/20/25mm	3050 x 1530 mm	Light grey similar	1350 kg/m ³
7	POM plastic panel, bevelled edges	10/20/30 mm	2000 x 1000 mm	White / Nature	1410 kg/m ³
8	PE plastic sheet, bevelled edges	10/20/30 mm	2000 x 1000 mm	White / Nature	935 kg/m ³
9	Screen printing board, bevelled edges	15/18/21/27/40mm	3000 x 1500 mm	Brown	850 kg/m ³
10	CDF panel, raw, bevelled edges	8/10/12/16/19 mm	2070 x 5600 mm	black similar	1000 kg/m ³

Other panel thicknesses and finishes available on request.