


## Threaded inserts




### Application

The threaded insert, which is manufactured with an external knurl, is inserted into a 12 mm hole across the line of the extrusion, enabling levelling feet and casters to be fixed to horizontal extrusions.

### Specification

Zinc-coated steel




### Application

Once the threaded insert has been pressed into the front side of extrusions B02-6/C03-4/, levelling feet or casters can be attached.

### Specification

Raw aluminium





### Application

The screw-in threaded insert is primarily used to take levelling feet and casters or to fix end panels or base plates in place.

Note that there is no thread around \* the hexagon socket.

### Specification

Zinc-coated steel



| Order data | Order number |
|------------|--------------|
|------------|--------------|

| Thread M | Extrusion base  |           |
|----------|-----------------|-----------|
|          | 50/45/40 (L=36) | 30 (L=28) |
| M10      | C33-20          | B33-20    |
| M8       | C33-22          | B33-22    |

| Measurement data | Order number |
|------------------|--------------|
|------------------|--------------|

| Thread | Extrusion type |       |
|--------|----------------|-------|
|        | B02-6          | C03-4 |
| M10    | ø 24.6         | 30    |
| M14    | ø 24.6         | 30    |
| M16    | ø 30           | 30    |
| M10    | ø 30.5         | 18    |

| Measurement data | Order number |
|------------------|--------------|
|------------------|--------------|

| Thread | Extrusion base |    |    |             |
|--------|----------------|----|----|-------------|
|        | M1             | M2 | S  | L           |
| M16    | M12            | 12 | 25 | 50/45/40 30 |
| M16    | M10            | 10 | 25 | A33-12      |
| M16    | M8             | 8  | 25 | A33-20 (-)  |
| M16    | M6             | 6  | 25 | A33-28 (-)  |
| M14    | M10            | 10 | 25 | A33-26      |
| M14    | M8             | 8  | 25 | B33-21 (-)  |
| M14    | M6             | 6  | 25 | B33-28      |
| M14    | M6             | 6  | 25 | B33-26      |

(-)=stainless steel