



Linear sliding block



Specification

Housing: aluminium, anodised in natural colours
 Linear bearing: steel, sealed on both sides, maintenance-free

Steel shafts




Application

The steel shafts are used in combination with the linear sliding block and the shaft clamping blocks assembled on the appropriate extrusion framework. This serves to create high load-bearing linear guides.

Specification

Steel, Cf 53, hardened, ground
 Hardness: HRc 62 ± 2
 Ø 12 0.9 Kg/m
 Ø 16 1.5 Kg/m



Load rating

dynamic	static
850 N	620 N

Order data Order number

Linear sliding block	L16-68
----------------------	--------

Order data Order number

Steel shaft Ø12	
Standard length 6000 mm	L12-20-01/6000
Cut to length	L12-20-02-02/...
Steel shaft Ø16	
Standard length 6000 mm	L16-20-01/6000
Cut to length	L16-20-02-02/...